

Video | SweetLine - Time-Saving Approach to Getting Better Optical Performance

Video SweetLine - Time-Saving Approach to Getting Better Optical Performance				
Published:	2019, October 1	Last Updated:	2019, December 5	v.2.0
Your browser does not support the HTML5 video element				
Video summary: - CrownAngle = 34.5 and PavilionAngle = 40.75 named <i>Tolkowsky Point</i> provide the best optical performance - Brilliants belonging to axis going through Tolkowsky Point with the negative slope 1:6 also provide excellent optical performance - The SweetLine parameter sticks solutions to this axis - There are two ways of using SweetLine: via SweetLine profile or using your own editable profile with SweetLine, CrownAngle and PavilionAngle set to your needs				
Video keywords: SweetLine, SweetLine axis, optical performance, CrownAngle, PavilionAngle				
Published in:	Release Notes	2019-10-23 - HPOxygen Server 5.3.42		
	Documentation	Using SweetLine		
	Playlists	All Videos		
	Also	As Separate Page Specification		